

## Declaration of compliance

77313 - Replacement Cassette, Hygienic, 250 mm, Blue Regarding following item:

> 77323 - Replacement Cassette, Hygienic, 400 mm, Blue 77333 - Replacement Cassette, Hygienic, 500 mm, Blue 77343 - Replacement Cassette, Hygienic, 600 mm, Blue 77353 - Replacement Cassette, Hygienic, 700 mm, Blue

Vikan A/S Business operator:

Rævevei 1 7800 Skive Denmark

Tel.: +45 96 14 26 00

Materials: Polypropylene 98 %

> Monomers and additives used to manufacture this grade are listed in Commision Regulation (EU) No. 10/2011 of 14. January 2011 on plastic materials and articles intended to come into contact with foodstuffs. Current amendments 321/2011 (1. April 2011), 1282/2011 (10. December 2011) and 1183/2012 (30. November

No monomers with specific migration limit (SML) are used. Additives with specific migration limit are used. Specific migration limits for this material are still to be determined.

This material contains one or more dual use additives. The identity of this/these substance(s) can be disclosed for testing purposes upon special request. Further information can be given on request.

## The squeegee blade for 2C made from rubber 98 %

The Styrene Block Copolymer, the polypropylene resin and ethylene-vinyl acetate copolymer (EVA), used in the construction of this equipment, meet the relevant requirements of Framework Regulation 1935/2004/EC. with regard to plastic raw materials used for articles or components of articles intended to come into contact with food. The monomers, starting substances and additives (incl. the plasticiser) used are listed in Annex I of the consolidated Commission Regulation No.10 (2011), related to Plastic Materials and Articles intended to come into contact with foodstuffs). The mineral filler complies with EN71-3.

Applicable restrictions are available on request (supplier proprietary information).

## Blue masterbatch 2 %

Monomers and additives used to manufacture this grade are listed in Commision Regulation (EU) No. 10/2011 of 14. January 2011 on plastic materials and articles intended to come into contact with foodstuffs. Current admentments 321/2011 (1. April 2011) and 1282/2011 are included.

Following monomers and additives with specific migration limit (SML) are used:

Ref no. 13380/25600/94960, cas no. 77-99-6, 1,1,1-trimethylolpropan and ref. no 68320, cas no. 2082-79-3,

octadecyl-3-(3,5-di-tert-butyl-4- hydroxyphenyl) propionat.

Calculations have proven that the product meets the requirement regarding the SML.

FDA: All raw materials in this product are in compliance with FDA (Food and Drug

Administration in the USA) CFR 21.

In accordance with EU Commission Regulation no. 1935/2004 of October 2004 the product is intended for food EU Commission:

contact. The squeegee can be marked with the "glass & fork" symbol on the packaging or on the product itself

through moulding.

The product is produced according to EU Commission Regulation no. 2023/2006 of 22. December 2006 on good

manufacturing practices for materials and articles intended to come into contact with food (GMP).

Overall migration tests are made on similar products:

The test made on 3% Acetic acid for 15 minutes at 50 °C complies with the requirements in EU 10/2011. The test made on 50% Ethanol for 15 minutes at 50 °C complies with the requirements in EU 10/2011. The test made on olive for 15 minutes at 50 °C does not comply with the requirements in EU 10/2011

Max. temp.: 50 °C

Min. temp.: -20 °C

General: It is recommended that equipment is cleaned, disinfected and sterilised, as appropriate to it's intended use,

It is also important to clean, disinfect and sterilise equipment as appropriate after use, using the appropriate

decontamination chemicals, concentrations, times and temperatures.

Appropriate equipment decontamination will minimise the risk of microbial growth and cross contamination and will maximise the efficiency and durability of the equipment.

Max. Wash temp.: 121 °C

Date:

Usage temperature:

Made by: Inger Arensbach

Quality- and environmental manager